



U GROUP SRL
Via Borgomanero n° 1
28040 Paruzzaro (NO)

LEGAL DATA:
C.F e Reg.Imp.Novara:02041920030
CCIAA Novara REA: 211799
P.IVA: IT02041920030
Codice Export: No015724
Cap.Soc.: 119.000 lv

CONTACTS:
WEBSITE: www.u-power.it/it
EMAIL: info@u-power.it
TEL: +39 0322 53 94 01
FAX: +39 0322 23 00 01

REV. 27/05/2024

DATA SHEET

PRODUCT PICTURE

RANGES

TECHNOLOGIES

RL20056 PUSH S1P SRC ESD
Natural Confort 11 Mondopoint
AirToe Aluminium
SHOE TYPE "A"
SIZE RANGE 35-48 (UK: 2-13)
Size tested: 42 - WEIGHT Kg 1,084



DESCRIPTION

TECHNICAL SPECIFICATIONS

EN ISO STANDARD

VALUE

Safety shoes low, light and comfortable U-Power of the Red Lion range, with ultra-breathable nylon and soft suede upper, aluminum toecap, anti-puncture, anti-slip and PU / PU infinergy, S1P SRC ESD sole

SAFETY TOE CAP "AirToe Aluminium"

Impact resistance. Free heights after collision mm
Compressive strength. Free heights after compr. mm

20345:2011

RESULT

≥ 14
≥ 14

17,5
17,0

INSOLE "Save & Flex PLUS® , pierce resistant "non metal" "

Puncture resistance N

≥ 1100

Compliant

ELECTRICAL RESISTANCE CATEGORY

Environmental class 1 - 12% humidity
Environmental class 2 - 25% humidity
Environmental class 3 - 50% humidity

10⁵ Ω e 10⁹ Ω (0,1 MΩ a 100 MΩ)
10⁵ Ω e 10⁹ Ω (0,1 MΩ a 100 MΩ)
10⁵ Ω e 10⁹ Ω (0,1 MΩ a 100 MΩ)

< 10⁸ Ohm
< 10⁸ Ohm
< 10⁸ Ohm

UPPER DYNAMIC WATERPROOFING AFTER 60'

Water absorption after 60'
Water transmitted after 60'
Permeability to water vapor mg/(cm² h)
Permeability coefficient mg/cm²

≤ 30%
≤ 0.2 gr
≥ 0.8
≥ 15

N.A.
N.A.
7,0
62,6

VAMP LINING

Permeability to water vapor mg/(cm² h)
Permeability coefficient mg/cm²
Resistance to abrasion - DRY cycles
Resistance to abrasion - WET cycles

≥ 2
≥ 20
25600 cycles
12800 cycles

23,7
189,7
No hole
No hole

INSOLE

Abrasion resistance

≥ 400 cycles

No damage

SOLE WEAR

Abrasion resistance (volume loss) mm³
Bending resistance mm
Resistance to sole / midsole detachment N/mm
Hydrocarbons resistance (% volume variation)
Heel energy absorption J
Adherence coef. with EN 13207 SRB method
Adherence coef. with EN 13207 SRA method

≤ 150
≤ 4
≥ 3
≤ 12
≥ 20
≥ 0.18
≥ 0.32

77
3,2
3,4
11,6
36
0,24
0,68